

# PDPM150L6F

APC 144kVA Modular Power Distribution Unit,  
Isolation Transformer, 600:208V, 72 Poles, 2  
Subfeed



## Overview

Presentation	A fully scalable power distribution system that cost-effectively provides high levels of availability and enables the quick addition of circuits and cord-sets.
Lead time	Usually Ships within 6 Weeks

## Main

Main Input Voltage	3 phase
Main Output Voltage	208 V 3 phase
Provided Equipment	Installation guide Network Management Card

## Physical

Color	Black
Height	79.02 in (200.7 cm)
Width	23.62 in (60 cm)
Depth	42.09 in (106.9 cm)
Net Weight	1942.27 lb(US) (881 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Not rack-mountable

## Input

Input Frequency	60 Hz
Max line current	141 A
Load Capacity	144000 VA

## Output

Protection Type	Circuit breaker
-----------------	-----------------

## Conformance

Product Certifications	CUL Listed CSA
Standards	UL 60950-1

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environmental

Ambient Air Temperature for Operation	23...104 °F (-5...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...9842 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

## Ordering and shipping details

GTIN	731304295402
Package weight(Lbs)	2043.69 lb(US) (927 kg)

## Packing Units

Package 1 Height	84.76 in (215.3 cm)
Package 1 width	40.00 in (101.6 cm)
Package 1 Length	47.99 in (121.9 cm)

## Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

## Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------