

Product data sheet

Characteristics

PDW10L21-20XC

10' CABLE EXTENDER 5-WIRE #10 AWG, UL WITH L21-20R/P



Overview

| | |
|-----------|------------------------------|
| Lead time | Usually Ships within 2 Weeks |
|-----------|------------------------------|

General

| | |
|--------------------|--------------------|
| Provided equipment | Installation guide |
|--------------------|--------------------|

Physical

| | |
|--------------|----------------------|
| Cable length | 10 ft (3.05 m) |
| Color | Black |
| Depth | 120.00 in (304.8 cm) |
| Height | 2.52 in (6.4 cm) |
| Net Weight | 3.53 lb(US) (1.6 kg) |
| Width | 2.01 in (5.1 cm) |

Input

| | |
|-----------------------|--------------|
| Plug standard | NEMA L21-20P |
| Permissible voltage | 200...250 V |
| Max line current | 20 A |
| Nominal Input Voltage | 3 phase |

Output

| | |
|--------------------------------------|------------------------|
| Maximum Total Current Draw per Phase | 20 A |
| Output voltage | 120 V 208 V 3 phase |

Conformance

| | |
|------------------------|-----------|
| Product certifications | UL Listed |
|------------------------|-----------|

Ordering and shipping details

| | |
|---------------------|-----------------------|
| GTIN | 00731304233091 |
| Package weight(Lbs) | 3.92 lb(US) (1.78 kg) |

Packing Units

| | |
|------------------|--------------------|
| Package 1 Height | 4.02 in (10.2 cm) |
| Package 1 width | 12.01 in (30.5 cm) |
| Package 1 Length | 17.52 in (44.5 cm) |

Offer Sustainability

| | |
|-------------------|---------------------|
| EU RoHS Directive | Under investigation |
|-------------------|---------------------|

Contractual warranty

| | |
|----------|---------------------------|
| Warranty | 2 years repair or replace |
|----------|---------------------------|