

# Product data sheet

## Characteristics

# PDW32L21-20XC

32' CABLE EXTENDER 5-WIRE #10 AWG, UL  
WITH L21-20R/P



## Overview

|           |                              |
|-----------|------------------------------|
| Lead time | Usually Ships within 2 Weeks |
|-----------|------------------------------|

## General

|                    |                    |
|--------------------|--------------------|
| Provided equipment | Installation guide |
|--------------------|--------------------|

## Physical

|            |                        |
|------------|------------------------|
| Color      | Black                  |
| Depth      | 384.02 in (975.4 cm)   |
| Height     | 2.52 in (6.4 cm)       |
| Net Weight | 10.32 lb(US) (4.68 kg) |
| Width      | 2.01 in (5.1 cm)       |

## Input

|                       |              |
|-----------------------|--------------|
| Plug standard         | NEMA L21-20P |
| Permissible voltage   | 200...240 V  |
| Max line current      | 20 A         |
| Nominal Input Voltage | 3 phase      |

## Output

|                                      |                        |
|--------------------------------------|------------------------|
| Maximum Total Current Draw per Phase | 20 A                   |
| Output voltage                       | 120 V<br>208 V 3 phase |

## Conformance

|                        |           |
|------------------------|-----------|
| Product certifications | UL Listed |
|------------------------|-----------|

## Ordering and shipping details

|                     |                        |
|---------------------|------------------------|
| GTIN                | 00731304233008         |
| Package weight(Lbs) | 10.91 lb(US) (4.95 kg) |

## Packing Units

|                  |                    |
|------------------|--------------------|
| Package 1 Height | 4.02 in (10.2 cm)  |
| Package 1 width  | 12.01 in (30.5 cm) |
| Package 1 Length | 17.52 in (44.5 cm) |

Offer Sustainability

|                   |                     |
|-------------------|---------------------|
| EU RoHS Directive | Under investigation |
|-------------------|---------------------|

Contractual warranty

|          |                           |
|----------|---------------------------|
| Warranty | 2 years repair or replace |
|----------|---------------------------|