

Product data sheet

Characteristics

RACSC201

InRow SC System 2 InRow SC units, 1 NetShelter SX Rack 600mm, and Rear Containment



Overview

Lead time

Special Order - Call for Quoted Lead Times

Main

Main Input Voltage	200 V
	208 V
	220 V
	230 V
	240 V
Plug standard	NEMA L6-20P
Number of rack unit	42U
Number of cables	1
Provided Equipment	Installation guide

General

Compressor Type	Rotary
Air Discharge Patterns	Horizontal
Intake Air	Rear Return
Refrigerant Charge	3 lb(US) (1.36 kg)
Air flow	1200 ft ³ /min (566.34 l/s)
Inrush current	56 A
Condensate Pump Capacity	1.3 Gal/hr(US) (0.00 m ³ /h)

Physical

Color	Black
Height	78.39 in (199.1 cm)
Width	47.24 in (120 cm)
Depth	50.12 in (127.3 cm)
Net Weight	1123.26 lb(US) (509.5 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Input power	2940 W
Input Frequency	60 Hz

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environmental

Acoustic level	80 dBA
----------------	--------

Communications & Management

Control panel	Multi-function LCD status and control console
---------------	---

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
---------------------------	---

REACH free of SVHC	Yes
--------------------	-----

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
-------------------	--

Contractual warranty

Warranty	1 year (parts only)
----------	---------------------