

Product data sheet

Characteristics

RM79696006

Electrode holder for liquid level control,
Harmony, use up to 350 degree C



Main

Range of Product	Harmony Control Relays
Product or Component Type	Level electrode holder
Accessory / separate part designation	Electrode for use up to 350 °C
Accessory / separate part destination	Liquid level control relay
Accessory / separate part category	Relay accessories
Maximum pressure	<= 15 kg/cm ²

Complementary

Material	Ceramic isolation Stainless steel
Thread type	3/8 BSP
Net Weight	0.33 lb(US) (0.15 kg)

Environment

Maximum ambient air temperature for operation	662 °F (350 °C)
---	-----------------

Ordering and shipping details

Category	22380-RELAYS-MEASUREMENT (RM17-RM35)
Discount Schedule	CP2
GTIN	3389110281750
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.98 in (2.5 cm)
Package 1 Width	1.57 in (4.0 cm)
Package 1 Length	3.46 in (8.8 cm)
Package 1 Weight	2.47 oz (70.0 g)
Unit Type of Package 2	S01
Number of Units in Package 2	14
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	5.91 in (15.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	2.68 lb(US) (1.214 kg)

Offer Sustainability

California proposition 65

WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

EU RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)  [EU RoHS Declaration](#)

Mercury free

Yes

China RoHS Regulation

 [China RoHS Declaration](#)

RoHS exemption information

 Yes

Contractual warranty

Warranty

18 months