

Product data sheet

Characteristics

RM79696014

Probe for liquid level control, Harmony,
1000mm, for high temperature conditions



Main

Range of Product	Harmony Control Relays
Product or Component Type	Level control probe
Accessory / separate part designation	Probe for high temperature conditions
Accessory / separate part destination	Control relay Measurement relay Boiler Pressure vessel
Accessory / separate part category	Relay accessories
Product Compatibility	RM35LM33MW RM4L
Maximum pressure	<= 25 kg/cm ²

Complementary

Length	39.37 in (1000 mm)
Material	Stainless steel 304
Shape of screw head	Hexagonal
Thread type	3/8 BSP
Net Weight	0.79 lb(US) (0.36 kg)

Environment

Ambient Air Temperature for Operation	392 °F (200 °C)
---------------------------------------	-----------------

Ordering and shipping details

Category	22380-RELAYS-MEASUREMENT (RM17-RM35)
Discount Schedule	CP2
GTIN	3389110282030
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	43.31 in (110.0 cm)
Package 1 Width	1.18 in (3.0 cm)
Package 1 Length	1.18 in (3.0 cm)
Package 1 Weight	9.17 oz (260.0 g)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

California proposition 65

WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

EU RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)  [EU RoHS Declaration](#)

Mercury free

Yes

China RoHS Regulation

 [China RoHS Declaration](#)

RoHS exemption information

 Yes

Contractual warranty

Warranty

18 months