



Product availability: Non-Stock - Not normally stocked in distribution facility

**Main**

Device short name	SKY
Enclosure type	Weatherproof enclosure dust and oil resistant indoor/outdoor Enclosure corrosion resistance indoor/outdoor
Mounting diameter	1.18 in (30 mm)
Provided equipment	Contact block 1 KA3 Legend plate 1 KN102RP

**Complementary**

Line Rated Current	10 A
Contacts type and composition	1 NC
Control type	Push-button 1 9001SKR3R
Device mounting	Surface
Electrical connection	Screw clamp terminal
Enclosure material	Polymeric
Marking	STOP
Operator profile	1 projecting push-button
Permissible voltage	<= 600 V

**Environment**

NEMA degree of protection	NEMA 3/4/4X/13
Product certifications	CE CSA LR25490 class 3211 03 UL listed file E42259 CCN NKCR

**Ordering and shipping details**

Category	21429 - 9001 SK,SKY
Discount Schedule	CS1
GTIN	00785901044581
Nbr. of units in pkg.	1
Package weight(Lbs)	1.8
Returnability	N
Country of origin	MX

**Offer Sustainability**

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1002 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and

---

----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

---

### Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---