

Product data sheet

Characteristics

SMT1500RM2UCUS

APC Smart-UPS, Line Interactive, 1500VA, Rackmount 2U, 120V, 6x NEMA 5-15R outlets, SmartConnect Port+SmartSlot, AVR, LCD, TAA



Main

Main Input Voltage	120 V
Main Output Voltage	120 V
Input Connection Type	NEMA 5-15P
Nb of power socket outlets	6 NEMA 5-15R
Provided equipment	CD with software

Physical

Color	Black
-------	-------

Input

Efficiency at full load	75...154 V adjustable
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains
----------------------------------	---------------------------------

Environmental

Relative Humidity	0...95 %
Storage Relative Humidity	0...95 %

Batteries & Runtime

Battery power in VAh	432 VAh runtime
Battery Charge Power (Watts)	144 W rated

Ordering and shipping details

GTIN	731304424420
------	--------------

Offer Sustainability

EU RoHS Directive	Under investigation
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.