

Product data sheet

Characteristics

SQR441U1LAW

Socket-outlet, X Series, 15A, decorator, tamper resistant, WiFi connected, light almond, matte finish



Main

Range	Square D X Series
Product or Component Type	Socket-outlet
Device Application	Power supply
Device presentation	Mechanism with fixing frame
Aesthetic name	X Series
Outlet poles configuration	2P + E
Outlet standard	NEMA
Socket additional information	Tamper resistant

Complementary

Body type	Decorator
Socket number	2
Number of gangs	1 gang
[Ie] rated operational current AC	15 A
[Ue] rated operational voltage	125 V
Network type	AC
Network Frequency	60 Hz
Mounting Mode	By screws
Device mounting	Flush
Material	Plastic strap Metal fixing frame
Color	Light almond
Surface Finish	Matte
Connections - terminals	Phase and neutral 2 screw terminal AWG 14...AWG 12) copper Earth 1 screw terminal copper
Earth circuit	Self earthing
Width	1.73 in (44 mm)
Height	4.06 in (103 mm)
Depth	1.73 in (44 mm)
Quantity per Set	1 piece

Ordering and shipping details

Category	09930-WD CONNECTED DEVICES
Discount Schedule	DE9
GTIN	3606482012615
Returnability	Yes
Country of origin	CN

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.17 in (10.6 cm)
Package 1 Width	2.13 in (5.4 cm)
Package 1 Length	2.17 in (5.5 cm)
Package 1 Weight	4.80 oz (136.0 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Height	4.45 in (11.3 cm)
Package 2 Width	4.61 in (11.7 cm)
Package 2 Length	11.02 in (28.0 cm)
Package 2 Weight	3.23 lb(US) (1.464 kg)
Unit Type of Package 3	PAL
Number of Units in Package 3	1920
Package 3 Height	47.24 in (120.0 cm)
Package 3 Width	39.37 in (100.0 cm)
Package 3 Length	47.24 in (120.0 cm)
Package 3 Weight	758.59 lb(US) (344.09 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: carbon black, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information

Contractual warranty

Warranty	2 year
----------	--------