



## Overview

|           |                  |
|-----------|------------------|
| Lead time | Usually in Stock |
|-----------|------------------|

## Main

|                  |   |
|------------------|---|
| Number of cables | 1 |
|------------------|---|

## Physical

|                     |                       |
|---------------------|-----------------------|
| Color               | Black<br>Silver       |
| Height              | 1.69 in (4.3 cm)      |
| Width               | 17.01 in (43.2 cm)    |
| Depth               | 7.01 in (17.8 cm)     |
| Net Weight          | 5.00 lb(US) (2.27 kg) |
| Mounting preference | No preference         |
| USB compatible      | No                    |

## Environmental

|                           |                                 |
|---------------------------|---------------------------------|
| Relative Humidity         | 5...95 %                        |
| Storage Relative Humidity | 0...95 %                        |
| Storage altitude          | 0...10000 ft (0.00...3048.00 m) |

## Batteries & Runtime

|                          |   |
|--------------------------|---|
| Included Battery Modules | 0 |
| Battery Slots Empty      | 0 |

## Ordering and shipping details

|                       |                        |
|-----------------------|------------------------|
| GTIN                  | 731304248002           |
| Nbr. of units in pkg. | 1                      |
| Package weight(Lbs)   | 7.00 lb(US) (3.173 kg) |

## Packing Units

|                              |                    |
|------------------------------|--------------------|
| Unit Type of Package 1       | PCE                |
| Package 1 Height             | 3.74 in (9.5 cm)   |
| Package 1 width              | 20.51 in (52.1 cm) |
| Package 1 Length             | 9.49 in (24.1 cm)  |
| Number of Units in Package 3 | 48                 |

## Offer Sustainability

|                             |                                                                                                                                 |
|-----------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status    | Green Premium product                                                                                                           |
| REACH Regulation            |  <a href="#">REACH Declaration</a>             |
| EU RoHS Directive           | Compliant  <a href="#">EU RoHS Declaration</a> |
| Mercury free                | Yes                                                                                                                             |
| RoHS exemption information  |  <a href="#">Yes</a>                           |
| Optimized Energy Efficiency | Energy efficient product                                                                                                        |
| Take-back                   | Take-back program available                                                                                                     |

## Contractual warranty

|          |                           |
|----------|---------------------------|
| Warranty | 2 years repair or replace |
|----------|---------------------------|