

Product data sheet

Characteristics

SYBT9-B4LL

APC High Performance Long Life 10 Yrs

Battery Module for Symmetra PX 48/96/160KW



Overview

Lead time Usually in Stock



Main

Battery Type	VRLA
Provided Equipment	Installation guide

Physical

Height	6.26 in (15.9 cm)
Width	16.85 in (42.8 cm)
Depth	27.56 in (70 cm)
Net Weight	221.45 lb(US) (100.45 kg)
Mounting Mode	Not rack-mountable

Conformance

Product Certifications	CE Eurobat General Purpose
Standards	UL 1778

Environmental

Ambient Air Temperature for Operation	64...81 °F (18...27 °C)
Operating altitude	0...3333 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	5...104 °F (-15...40 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Storage Relative Humidity	0...95 %

Batteries & Runtime

Battery Placement	Internal Battery
Battery blocks per string	4
Battery Slots Empty	0
Included Battery Modules	0
Battery Voltage	384 V
Battery Volt-Amp-Hour Capacity	3456 VAh

Ordering and shipping details

Package weight(Lbs)	236.78 lb(US) (107.4 kg)
---------------------	--------------------------

Packing Units

Package 1 Height	7.09 in (18 cm)
Package 1 width	23.62 in (60 cm)
Package 1 Length	31.89 in (81 cm)
Number of Units in Package 3	7

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Take-back	Take-back program available