

Overview

Lead time	Usually in Stock
-----------	------------------



Main

Battery Type	VRLA
Provided Equipment	Installation guide

Physical

Height	6.26 in (15.9 cm)
Width	4.21 in (10.7 cm)
Depth	27.56 in (70 cm)
Net Weight	337.31 lb(US) (153 kg)
Mounting Mode	Not rack-mountable

Conformance

Product Certifications	CUL Listed Eurobat General Purpose UL Listed VDE
------------------------	---

Environmental

Ambient Air Temperature for Operation	64...81 °F (18...27 °C)
Operating altitude	0...3333 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	5...104 °F (-15...40 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Storage Relative Humidity	0...95 %

Batteries & Runtime

Battery Placement	Internal Battery
Battery blocks per string	6
Battery Slots Empty	0
Included Battery Modules	0
Battery Life	3...5 year(s)
Device mounting	Enclosed battery cartridge
Battery Voltage	384 V
Battery Volt-Amp-Hour Capacity	5184 VAh

Ordering and shipping details

Package weight(Lbs)	354.75 lb(US) (160.91 kg)
---------------------	---------------------------

Packing Units

Package 1 Height	7.09 in (18 cm)
Package 1 width	25.51 in (64.8 cm)
Package 1 Length	31.89 in (81 cm)
Number of Units in Package 3	7

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Take-back	Take-back program available

Contractual warranty

Warranty	1 year (parts only)
----------	---------------------