

Product data sheet

Characteristics

SYCFXR8S

Symmetra PX40KW Extended Run Battery Frame with Startup



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Number of cables	1
Battery Type	VRLA
Provided Equipment	Installation guide Start-Up Service User Manual

Physical

Color	Black
Height	82.01 in (208.3 cm)
Width	24.02 in (61 cm)
Depth	34.02 in (86.4 cm)
Net Weight	551.16 lb(US) (250 kg)
Mounting Mode	Not rack-mountable

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Operating altitude	0...3333 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %

Batteries & Runtime

Battery Slots Empty	8
Included Battery Modules	0
Battery Life	3...5 year(s)
Device mounting	Enclosed battery cabinet

Ordering and shipping details

Package weight(Lbs)	601.27 lb(US) (272.73 kg)
---------------------	---------------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Package 1 Height	82.01 in (208.3 cm)
Package 1 width	30.00 in (76.2 cm)
Package 1 Length	40.00 in (101.6 cm)
Number of Units in Package 3	2

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Lead free	Yes
Take-back	Take-back program available

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------