



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	3 phase
Number of cables	1
Battery Type	VRLA
Provided Equipment	Installation guide Start-Up Service User Manual

Physical

Color	Black
Height	82.01 in (208.3 cm)
Width	22.01 in (55.9 cm)
Depth	34.02 in (86.4 cm)
Net Weight	2104.42 lb(US) (954.55 kg)

Input

Input Frequency	50/60 Hz +/- 5 Hz auto sensing
Number of input connectors	1 Hard Wire 4-wire (3PH + G)

Conformance

Product Certifications	Eurobat General Purpose
------------------------	-------------------------

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Operating altitude	0...3333 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %

Batteries & Runtime

Battery Placement	Battery Cabinet
Battery blocks per string	32
Battery Slots Empty	0
Included Battery Modules	8
Battery manufacturer	Panasonic
Device mounting	Enclosed battery cabinet
Battery Voltage	192V

Ordering and shipping details

Package weight(Lbs)	2204.62 lb(US) (1000 kg)
---------------------	--------------------------

Packing Units

Package 1 Height	90.98 in (231.1 cm)
Package 1 width	30.00 in (76.2 cm)
Package 1 Length	40.00 in (101.6 cm)
Number of Units in Package 3	2

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Lead free	Yes
Take-back	Take-back program available

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------