



Overview

Presentation	High density, double-conversion on-line power protection with scalable runtime.
Lead time	Usually in Stock

Physical

Number of rack unit	0U
Depth	23.23 in (59 cm)
Height	5.90 in (14.99 cm)
Product Weight	33.07 lb(US) (15 kg)
Width	9.84 in (24.99 cm)

Input

Input Frequency	50/60 Hz +/- 5 Hz auto-sensing
Nominal Input Voltage	200 V 208 V 3 phase

Output

Kw Rating	2800 W
Max Configurable Power (Watts)	2800 W
Output voltage	200 V 208 V 230 V

Batteries & Runtime

Included Battery Modules	0
Battery Slots Empty	0
Liquid Electrolyte Value	0

Ordering and shipping details

GTIN	00731304007357
Package weight(Lbs)	40.08 lb(US) (18.18 kg)

Packing Units

Package 1 Height	17.30 in (43.94 cm)
Package 1 width	13.00 in (33.02 cm)
Package 1 Length	31.10 in (78.99 cm)

Offer Sustainability

EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes