



Main

Range of Product	ConneXium
Product or Component Type	Ethernet TCP/IP managed switch
Concept	Transparent Ready
Communication port protocol	Ethernet TCP/IP SSH HTTP HTTPS SNMP RS232 LLDP Telnet SNTP MRP (Media Redundancy Protocol)
Port Ethernet	10/100BASE-TX - 16 copper cable
Maximum number of switches in cascade	Unlimited
Cybersecurity	Port hardening

Complementary

Integrated connection type	Shielded RJ45 copper cable
Transmission support medium	Twisted shielded pairs cable CAT 5E copper cable
Maximum cable distance between devices	328.08 ft (100 m) copper cable
Ethernet service	Configuration via web server VLAN Multicast filtering Data stream control IGMP Snooping SNMP-Traps and SYSLOG
Communication Service	TFTP Quality of Service (QoS) Port monitoring Port mirroring Address conflict detection
Diagnostics run time	Signal contact Self test
Maximum number of switches in a ring	50
Redundancy	HIPER ring RSTP Redundant network coupling
[Us] rated supply voltage	12...48 V
Supply voltage limits	9.6...60 V DC SELV 18...30 V AC SELV
Power consumption in W	9.4 W
Electrical connection	Removable connector 6 ways power supply
Mounting Support	35 mm symmetrical DIN rail
Marking	CE UL RCM EtherNet/IP
Function Available	Alarms (Traps) System information Report Trap log

Local signalling	For P1 P2 power supplies 1 dual colour LED (green/yellow) For fault 1 LED (red) For ring manager 1 dual colour LED (green/yellow) For stand-by 1 LED (green) For link status 1 LED per channel (green) For ACT 1 LED per channel (yellow) Device status
Alarm output	1 voltfree contact 1 A
Alarm function	Power supply fault Data link status Redundancy ring fault Switch fault
Ethernet cabling system	TF switches
Width	4.37 in (111 mm)
Height	5.16 in (131 mm)
Depth	4.37 in (111 mm)
Net Weight	1.32 lb(US) (0.6 kg)

Environment

Ambient Air Temperature for Operation	32...140 °F (0...60 °C)
Relative Humidity	10...95 % non-condensing
IP Degree of Protection	IP20
Directives	2014/35/EU - low voltage directive 2014/30/EU - electromagnetic compatibility
Standards	UL 508 EN/IEC 61131 IEC 61850-3
Product certifications	CE UL RCM ODVA EtherNet/IP BV GL

Ordering and shipping details

Category	18225-PLC NTWRK HRDWR & PROWORX SOFTWARE
Discount Schedule	PC41
GTIN	3595863892468
Nbr. of units in pkg.	1
Package weight(Lbs)	29.28 oz (830.0 g)
Returnability	No
Country of origin	DE

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	5.12 in (13 cm)
Package 1 width	6.30 in (16 cm)
Package 1 Length	9.45 in (24 cm)
Unit Type of Package 2	S04
Number of Units in Package 2	8
Package 2 Weight	14.64 lb(US) (6.64 kg)
Package 2 Height	11.81 in (30 cm)
Package 2 width	15.75 in (40 cm)
Package 2 Length	23.62 in (60 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------

Dimensions

