

Product data sheet

Specifications



Terminal block, Linergy TR, green-yellow, 4mm², protective earth, 2 points, Set of 50

NSYTRV42PE

Product availability: Stock - Normally stocked in distribution facility

Main

Range	Linergy
Product name	Linergy TR
Product or Component Type	Terminal block
Device short name	TRV
Terminal block type	Protective earth
Terminal block level	1
Mounting Mode	Clip-on
Nominal cross section	0.006 in ² (4 mm ²)
Length	1.9 in (47.7 mm)
color	Green-yellow
Quantity per Set	Set of 50

Complementary

Width	0.2 in (6.2 mm)
Height	1.9 in (47.5 mm)
Connections - terminals	1 x screw terminal upstream 1 x screw terminal downstream
number of connections	2
Connection position	Sideways
Number of measurement input	2
Cable cross section	0.0002...0.009 in ² (0.14...6 mm ²), solid 0.0003...0.006 in ² (0.2...4 mm ²), flexible with cable end 0.0002...0.009 in ² (0.14...6 mm ²), flexible without cable end
Tightening torque	5.3...7.08 lbf.in (0.6...0.8 N.m)
Wire stripping length	0.4 in (9 mm)
Tool type	Connection screwdriver Disconnection screwdriver
Material	Polyamide 6/6: insulating case
Dielectric loss	0.01 at 1 MHz IEC 60250 0.01 at 1 MHz VDE 0303-T4
Dielectric constant	3.7 at 1 MHz
Resistivity	10000 MΩ.m IEC 60093 10000 MΩ.m VDE 0303-T30
Surface resistance	1000 GΩ IEC 60093 1000 GΩ VDE 0303-T30

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Creep resistance	500 CTI (> 400 kB) IEC 60093 500 CTI (> 400 kB) VDE 0303-T30
Flame retardance	V0 0.03 in (0.8 mm) UL 94
Product Weight	0.47 oz (13.38 g)
Range compatibility	PrismaSeT G PrismaSeT P PrismaSeT Pack 250 PanelSeT TeSys Mureva PrismaSeT XS
Product Compatibility	Spacial enclosures

Environment

Product Certifications	VDE CSA GL DNV UL
Dielectric strength	1000 V IEC 60243-1
Ambient air temperature for operation	-40...266 °F (-40...130 °C) IEC 60216-1 -40...266 °F (-40...130 °C) VDE 0304-T21

Ordering and shipping details

Category	US10CP521715
Discount Schedule	0CP5
GTIN	3606480531965
Returnability	Yes
Country of origin	DE

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	0.31 in (0.800 cm)
Package 1 Width	1.89 in (4.800 cm)
Package 1 Length	1.89 in (4.800 cm)
Package weight(Lbs)	0.459 oz (13.000 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	50
Package 2 Height	1.97 in (5.000 cm)
Package 2 Width	2.28 in (5.800 cm)
Package 2 Length	12.60 in (32.000 cm)
Package 2 Weight	23.915 oz (678.000 g)
Unit Type of Package 3	P06
Number of Units in Package 3	10400
Package 3 Height	29.53 in (75.000 cm)
Package 3 Width	23.62 in (60.000 cm)

Package 3 Length

31.50 in (80.000 cm)

Package 3 Weight

334.979 lb(US) (151.944 kg)

Contractual warranty

Warranty

18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO₂ eq, Total Life cycle) **6**

Environmental Disclosure [Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard **Yes**

Packaging without single use plastic **Yes**

[EU RoHS Directive](#) **Compliant with Exemptions**

SCIP Number **8e5413ff-f1a1-4909-ad03-977097e33bd2**

REACH Regulation [REACH Declaration](#)

California proposition 65

WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](#)

Halogen content performance **Halogen free plastic parts product**

Use Again

Repack and remanufacture

Circularity Profile **No need of specific recycling operations**

Take-back **No**

WEEE Label **The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.**