

Product data sheet

Specifications



NFC cartridge fuses, TeSys GS, cylindrical, 22mm x 58mm, fuse type aM, 690VAC, 40A, without striker, set of 10 parts

DF2FA40

Main

Range of product	TeSys fuse-disconnector
Product or component type	Cartridge fuse
Device short name	DF2
[Ue] rated operational voltage	690 V AC
Fuse size	22 x 58 mm
Fuse type	NFC
Quantity per set	Set of 10

Complementary

[In] rated current	40 A 690 V
fuse curve	AM
Product weight	0.045 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.4 cm
Package 1 Width	11.8 cm
Package 1 Length	12.0 cm
Package 1 Weight	49.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	2.4 cm
Package 2 Width	11.8 cm
Package 2 Length	12.0 cm
Package 2 Weight	494.0 g
Unit Type of Package 3	S01
Number of Units in Package 3	120
Package 3 Height	15.0 cm
Package 3 Width	15.0 cm
Package 3 Length	40.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 3 Weight	6.62 kg
------------------	---------

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant
REACH Regulation	REACH Declaration
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
PVC free	Yes

Use Again

 Repack and remanufacture	
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins