

Product data sheet

Specifications



Head for selector switch, Harmony 9001SK, plastic, standard handle, black, 30mm, 3 positions, return both sides to center, cam code 2

9001SKS52B

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

| | |
|---------------------------|--------------------------|
| Range of Product | Harmony 9001SK |
| Product or Component Type | Head for selector switch |
| Device short name | 9001SK |

Complementary

| | |
|-------------------------------|-----------------------|
| Bezel material | Plastic |
| Mounting diameter | 1.2 in (30 mm) |
| Operator position information | 3 positions |
| Contacts type and composition | Without contact block |
| Device presentation | Basic element |
| Cap/operator or lens colour | Black |
| Operator profile | Standard handle |
| Type of operator | Spring return |
| Size | 30 mm |
| Return | Both sides to centre |
| Cam profile | 2 |

Environment

| | |
|---------------------------------------|---|
| Protective treatment | TC |
| Ambient Air Temperature for Storage | -40...158 °F (-40...70 °C) |
| Ambient Air Temperature for Operation | -13...158 °F (-25...70 °C) |
| Electrical shock protection class | Class II conforming to IEC 61140 |
| IP degree of protection | IP66 IEC 60529 |
| NEMA degree of protection | NEMA 1/2/3/3R/4/4X/6/12/13 |
| Product Certifications | UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03 CE |

Ordering and shipping details

| | |
|-------------------|--------------|
| Category | US10CS121429 |
| Discount Schedule | 0CS1 |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| | |
|-------------------|--------------|
| GTIN | 785901959878 |
| Returnability | No |
| Country of origin | MX |

Packing Units

| | |
|------------------------------|--------------------|
| Unit Type of Package 1 | PCE |
| Nbr. of units in pkg. | 1 |
| Package 1 Height | 3.03 in (7.7 cm) |
| Package 1 Width | 7.64 in (19.4 cm) |
| Package 1 Length | 19.37 in (49.2 cm) |
| Package weight(Lbs) | 2.08 oz (59 g) |
| Unit Type of Package 2 | S01 |
| Number of Units in Package 2 | 14 |
| Package 2 Height | 5.91 in (15 cm) |
| Package 2 Width | 5.91 in (15 cm) |
| Package 2 Length | 15.75 in (40 cm) |
| Package 2 Weight | 24.0 oz (680 g) |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Environmental Disclosure

[Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard Yes

Packaging without single use plastic Yes

[EU RoHS Directive](#) Pro-active compliance (Product out of EU RoHS legal scope)

California proposition 65

WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

Repack and remanufacture

Circularity Profile No need of specific recycling operations

Take-back No

WEEE Label The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.