

Product data sheet

Specifications



variable speed drive, SFlex Altivar
212, 460V AC, 3 phase, 1hp,
enclosed drive

SFD212CG4YB07D07

Product availability: Stock - Normally stocked in distribution facility

Main

Product or Component Type	Variable speed drive
Motor power kW	0.75 kW
Maximum Horse Power Rating	1 hp
Nominal output current	2.1 A 460 V

Ordering and shipping details

Category	US1CP4D22199
Discount Schedule	CP4D
GTIN	785901004516
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	21.30 in (54.1 cm)
Package 1 Width	22.28 in (56.6 cm)
Package 1 Length	48.50 in (123.2 cm)
Package weight(Lbs)	89.0007 lb(US) (40.37 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
EU RoHS Directive	Not compliant
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov