

Product data sheet

Specifications



variable speed drive, SFlex Altivar 212, 460V AC, 3 phase, 3hp, enclosed drive

SFD212EG4YB07D07

Product availability: Stock - Normally stocked in distribution facility

Main

Product or Component Type	Variable speed drive
Motor power kW	2.2 kW
Maximum Horse Power Rating	3 hp
Nominal output current	4.8 A 460 V

Ordering and shipping details

Category	US1CP4D22199
Discount Schedule	CP4D
GTIN	785901264859
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	15.12 in (38.4 cm)
Package 1 Width	12.91 in (32.8 cm)
Package 1 Length	48.50 in (123.2 cm)
Package weight(Lbs)	64.999 lb(US) (29.483 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances

EU RoHS Directive

Not compliant

California proposition 65

WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov