

# Product data sheet

Specifications

## APC NetShelter Power Cord, C19 to IEC309 16A, 2.5m



AP9876

### Overview

Lead time Usually in Stock

### Main

Product or component type	Power cord
Input Connection Type	IEC 60309 16 A
Cable length	2.5 m
Number of cables	1

### Physical

Colour	Black
Product weight	0.24 kg
Mounting preference	No preference
Mounting mode	Not rack-mountable

### Input

Network frequency	50/60 Hz
permissible voltage	90...250 V
Max line current	16 A
Input current limits	16 A

### Output

Max current draw	16 A
Number of power socket outlets	1 IEC 60320 C19
Protection type	Without circuit breaker

### Conformance

Product certifications	VDE
------------------------	-----

### Environmental

Ambient air temperature for operation	0...45 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

---

Storage Relative Humidity	0...95 %
Storage altitude	0...15240 m

---

## Packing Units

---

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.1 cm
Package 1 Width	10.2 cm
Package 1 Length	20.3 cm
Package 1 Weight	0.299 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Height	23.3 cm
Package 2 Width	32.5 cm
Package 2 Length	53 cm
Package 2 Weight	5.1 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	10
Package 3 Height	143.99 cm
Package 3 Width	100 cm
Package 3 Length	120 cm
Package 3 Weight	5.1 kg

---

## Contractual warranty

---

Warranty	2 years repair or replace
----------	---------------------------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

Total lifecycle Carbon footprint **76**

Environmental Disclosure [Product Environmental Profile](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard **No**

Packaging without single use plastic **No**

[EU RoHS Directive](#) **Compliant**

SCIP Number **1cdb2fed-a06f-4574-913d-8df8e70936b2**

REACH Regulation [REACH Declaration](#)

California proposition 65  
WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

Halogen-free status **Product contains halogen above thresholds**

## Use Again

### Repack and remanufacture

End of life manual availability [End of Life Information](#)

Take-back **No**

WEEE Label  
 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Image of product / Alternate images

Alternative

---

