

Product data sheet

Specifications

SQUARE D



Timer, Harmony 9050 JCK, off delay, adjustable time, 0.3 to 30 minutes, 10A, 240V AC, 120V AC/110V DC

9050JCK27V20

Product availability: Stock - Normally stocked in distribution facility

Main

product range	9050JCK
product type	Timer
timing mode	Off-delay
timing range	0.3...30 min
supply voltage	120 V AC 110 V DC

Complementary

power consumption	2 VA
current rating	10 A
switch function	DPDT
contact composition	2 NO + 2 NC
contact material	Silver nickel
maximum switching voltage	240 V AC
mounting type	Socket
number of pins	11
shape of pins	Tubular
for use with	8501NR61 8501NR62

Environment

certifications	CE UL Recognized UL Listed
ambient temperature range - operational	-28...66 °C (-18...150 °F)
Height	2.4 in (61 mm)
Width	1.7 in (43 mm)
Depth	4.09 in (104 mm)

Ordering and shipping details

Category	US10CP221651
Discount Schedule	OCP2
GTIN	785901032670

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	1.90 in (4.826 cm)
Package 1 Width	4.40 in (11.176 cm)
Package 1 Length	2.60 in (6.604 cm)
Package weight(Lbs)	5.280 oz (149.686 g)

Contractual warranty

Warranty	18 months
----------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle)	50
--	----

Use Better

Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)

Use Again

Repack and remanufacture

Take-back	No
-----------	----

Image of product / Alternate images

Alternative



