



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	208 V
Main Output Voltage	200 V 208 V
Plug standard	NEMA L6-30P
Number of rack unit	0U
Cable length	10 ft (3.05 m)
Provided Equipment	Installation guide Safety guide

Physical

Color	Black
Height	32.80 in (83.3 cm)
Width	2.20 in (5.6 cm)
Depth	1.85 in (4.7 cm)
Net Weight	6.13 lb(US) (2.78 kg)
Mounting Location	Side
Mounting preference	Lower
Mounting Mode	Not rack-mountable

Input

Line Rated Current	24 A
Acceptable Input Voltage	200...240 V
Max line current	30 A
Input current limits	30 A
Load Capacity	5000 VA
Input Frequency	50/60 Hz

Output

Number of power socket outlets	14 IEC 60320 C13 2 IEC 60320 C19
--------------------------------	-------------------------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Conformance

Product Certifications	CUL Listed UL Listed
------------------------	-------------------------

Environmental

Ambient Air Temperature for Operation	32...122 °F (0...50 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...149 °F (-15...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	731304327639
Package weight(Lbs)	7.14 lb(US) (3.24 kg)

Packing Units

Package 1 Height	38.03 in (96.6 cm)
Package 1 width	6.14 in (15.6 cm)
Package 1 Length	5.39 in (13.7 cm)
SCC14	10731304327636
Number of Units in Package 3	60

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Lead free	Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------