



### Overview

Lead time	Usually in Stock
-----------	------------------

### Main

Main Input Voltage	208 V
Main Output Voltage	208 V
Plug standard	IEC 60309 60 A 2P + PE
Number of rack unit	0U
Cable length	10 ft (3.05 m)
Number of cables	1
Provided Equipment	Installation guide Safety guide

### Physical

Height	64.02 in (162.6 cm)
Width	2.20 in (5.6 cm)
Depth	1.69 in (4.3 cm)
Net Weight	20.24 lb(US) (9.18 kg)
Mounting Location	Rear
Mounting preference	No preference
Mounting Mode	Not rack-mountable

### Input

Line Rated Current	45 A
Acceptable Input Voltage	200...240 V
Max line current	60 A
Input current limits	60 A
Load Capacity	10000 VA
Input Frequency	50/60 Hz

### Output

Number of power socket outlets	21 IEC 60320 C13 6 IEC 60320 C19
--------------------------------	-------------------------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Conformance

Product Certifications	CUL Listed UL Listed
------------------------	-------------------------

## Environmental

Ambient Air Temperature for Operation	32...122 °F (0...50 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...149 °F (-15...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

## Ordering and shipping details

GTIN	731304327776
Package weight(Lbs)	24.25 lb(US) (11 kg)

## Packing Units

Package 1 Height	73.82 in (187.5 cm)
Package 1 width	8.90 in (22.6 cm)
Package 1 Length	5.31 in (13.5 cm)
Number of Units in Package 3	35

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Lead free	Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------