



Overview

Presentation	This unique Y cable takes a single C20 input and splits it into two C19 outlets. This allows for multiple outputs to be connected to a single output on a rack PDU
Lead time	Usually in Stock

Main

Main Output Voltage	208 V
Input Connection Type	IEC 60320 C20
Cable length	6 ft (1.83 m)

Physical

Color	Black
Height	2.01 in (5.1 cm)
Width	10.51 in (26.7 cm)
Depth	3.50 in (8.9 cm)
Net Weight	1.41 lb(US) (0.64 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Max line current	20 A
Input current limits	20 A

Output

Number of power socket outlets	1 IEC 60320 C19
--------------------------------	-----------------

Conformance

Product Certifications	UL Listed
------------------------	-----------

Environmental

Ambient Air Temperature for Operation	14...104 °F (-10...40 °C)
Relative Humidity	20...80 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	50...86 °F (10...30 °C)
Storage Relative Humidity	20...80 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

Category	11309-APC RESALE PRODUCTS
Discount Schedule	APC1
GTIN	731304241751
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	US

Packing Units

Package 1 Height	3.39 in (8.6 cm)
Package 1 width	12.76 in (32.4 cm)
Package 1 Length	4.02 in (10.2 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Lead free	Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------