

# Product data sheet

Specifications

SQUARE D



Plug in relay, Type R, miniature, 1 HP at 277 VAC, 15A resistive at 120 VAC, 5 blade, SPDT, 1 NO, 1 NC, 120 VAC coil

8501RS41P14V20

Product availability: Stock - Normally stocked in distribution facility

## Main

product range	8501R
product type	Miniature Relay
Relay Type	Standard

## Complementary

mounting type	Socket
contact composition	SPDT
[Uc] control circuit voltage	120 V AC
pilot light	Green indicator relay energised LED
manual operator	Without test button
horsepower rating	0.5 120 V AC 1 277 V AC
breaking capacity	3 A 120 V AC inductive control circuit UL 508 1.5 A 240 V AC inductive control circuit UL 508 15 A 120 V AC resistive control circuit UL 508 10 A 277 V AC resistive control circuit UL 508 15 A 28 V DC resistive control circuit UL 508
maximum switching voltage	300 V AC 30 V DC
contact material	Silver alloy, gold flashed
operating time	20 ms - pick-up 20 ms - drop-out
shape of pins	Spade
for use with	8501NR41
Height	1.07 in (27.3 mm)
Width	0.6 in (14 mm)
Depth	1.6 in (41.8 mm)

## Environment

ambient temperature range - operational	-40...55 °C (-40...131 °F)
product certifications	UL Listed UL Recognized CSA CE

## Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Category	US10CP221143
Discount Schedule	0CP2
GTIN	785901218487
Returnability	Yes
Country of origin	CN

## Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	1.18 in (3.0 cm)
Package 1 Width	1.38 in (3.5 cm)
Package 1 Length	2.17 in (5.5 cm)
Package weight(Lbs)	1.0 oz (28.0 g)

## Contractual warranty

Warranty	18 months
----------	-----------

## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Use Better

 <b>Materials and Substances</b>	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
<a href="#">EU RoHS Directive</a>	Pro-active compliance (Product out of EU RoHS legal scope)
REACH Regulation	<a href="#">REACH Declaration</a>
California proposition 65	<b>WARNING:</b> This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

### Use Again

 <b>Repack and remanufacture</b>	
Take-back	No