

Product data sheet

Specifications



RJ45 COVER

ZARC52

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range of Product	Harmony eXLhoist
Accessory / Separate Part Type	Pre-wired connector
Accessory / separate part category	Connection accessory

Complementary

Product compatibility	Control station ZARB
Material	PE (polyethylene)

Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...140 °F (-40...60 °C)
IP Degree of Protection	IP65
NEMA Degree of Protection	NEMA 4

Ordering and shipping details

Category	US10CS222479
Discount Schedule	0CS2
GTIN	3606480982576
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	0.67 in (1.7 cm)
Package 1 Width	3.15 in (8.0 cm)
Package 1 Length	4.72 in (12.0 cm)
Package weight(Lbs)	0.6 oz (17.0 g)
Unit Type of Package 2	S01
Number of Units in Package 2	5
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	5.91 in (15.0 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 2 Length 15.75 in (40.0 cm)

Package 2 Weight 12.6 oz (357.0 g)

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Under investigation

Use Again

 Repack and remanufacture	
Take-back	No