



### Overview

Lead time	Usually Ships within 8 Weeks
-----------	------------------------------

### Main

Battery Type	VRLA
Provided Equipment	Installation guide User Manual

### Physical

Color	Black
Height	78.39 in (199.1 cm)
Width	23.62 in (60 cm)
Depth	42.13 in (107 cm)
Net Weight	2665.39 lb(US) (1209 kg)
USB compatible	No

### Conformance

Product Certifications	CE Eurobat General Purpose
Standards	EN/IEC 62040-1-1 EN/IEC 62040-2 EN/IEC 62040-3 UL 1778

### Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Operating altitude	0...3333 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	5...104 °F (-15...40 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Storage Relative Humidity	0...95 %

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Batteries & Runtime

Battery blocks per string	4
Battery Slots Empty	0
Included Battery Modules	9
Device mounting	19 inch Battery tray
Additional information	Request SYBT9-B4 for replacement battery

## Ordering and shipping details

Package weight(Lbs)	2960.81 lb(US) (1343 kg)
---------------------	--------------------------

## Packing Units

Package 1 Height	84.02 in (213.4 cm)
Package 1 width	33.39 in (84.8 cm)
Package 1 Length	47.64 in (121 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Lead free	Yes
Take-back	Take-back program available

## Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------