

Product data sheet

Specifications



NFC cartridge fuses, TeSys GS, cylindrical 10mm x 38mm, fuse type gG, 400VAC, 32A, without striker, set of 10 parts

DF2CN32

Main

Range of product	TeSys fuse-disconnector
Product or component type	Cartridge fuse
Device short name	DF2
[Ue] rated operational voltage	400 V AC
[In] rated current	32 A 400 V
Fuse size	10 x 38 mm
Fuse type	NFC
Quantity per set	Set of 10

Complementary

fuse curve	GG
Product weight	0.01 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.300 cm
Package 1 Width	5.500 cm
Package 1 Length	8.000 cm
Package 1 Weight	8.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	1.300 cm
Package 2 Width	5.500 cm
Package 2 Length	8.000 cm
Package 2 Weight	80.000 g
Unit Type of Package 3	S02
Number of Units in Package 3	720
Package 3 Height	15.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm

Package 3 Weight 5.827 kg

Contractual warranty

Warranty 18 months



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant
REACH Regulation	REACH Declaration
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
PVC free	Yes

Use Again

 Repack and remanufacture	
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins