



Main

Product or Component Type	Reversing Hoist Contactor
Line Rated Current	40 A
Maximum Horse Power Rating	3 Hp 115 V AC, 1 phase 7.5 Hp 230 V AC, 1 phase 15 Hp 230 V AC, 3 phase 20 Hp 460 V AC, 3 phase 20 hp 575 V AC, 3 phase

Complementary

Product Certifications	UL Listed CSA
[Ue] rated operational voltage	600 V AC
Poles description	3P
[Uc] control circuit voltage	24 V AC 50/60 Hz
Phase	3 phase
Range of Product	DPR

Ordering and shipping details

Category	21403-8965DPR1>DPR4 - 20A>40A REV HOIST
Discount Schedule	CP1
GTIN	785901571568
Returnability	No
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.00 in (12.7 cm)
Package 1 Width	5.00 in (12.7 cm)
Package 1 Length	6.00 in (15.24 cm)
Package 1 Weight	32.00 oz (907.185 g)

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------