



## Overview

|           |                  |
|-----------|------------------|
| Lead time | Usually in Stock |
|-----------|------------------|

## General

|                    |                                                                                                |
|--------------------|------------------------------------------------------------------------------------------------|
| Provided Equipment | All required connectors<br>Battery recycling guide<br>Installation guide<br>Reusable packaging |
|--------------------|------------------------------------------------------------------------------------------------|

## Physical

|                |                         |
|----------------|-------------------------|
| Depth          | 22.99 in (58.4 cm)      |
| Height         | 2.99 in (7.6 cm)        |
| Product Weight | 49.10 lb(US) (22.27 kg) |
| Width          | 7.99 in (20.3 cm)       |

## Environmental

|                                       |                                  |
|---------------------------------------|----------------------------------|
| Ambient Air Temperature for Operation | 32...104 °F (0...40 °C)          |
| Operating altitude                    | 0...10000 ft                     |
| Relative Humidity                     | 0...95 %                         |
| Ambient Air Temperature for Storage   | 5...113 °F (-15...45 °C)         |
| Storage altitude                      | 0...50000 ft (0.00...15240.00 m) |
| Storage Relative Humidity             | 0...95 %                         |

## Batteries & Runtime

|                           |                            |
|---------------------------|----------------------------|
| Battery blocks per string | 10                         |
| Battery Slots Empty       | 0                          |
| Included Battery Modules  | 0                          |
| Device mounting           | Enclosed battery cartridge |
| Battery Voltage           | 120 V                      |
| Battery Type              | Lead-Acid battery          |
| RBC Quantity              | 1                          |

## Ordering and shipping details

|                     |                         |
|---------------------|-------------------------|
| Package weight(Lbs) | 55.51 lb(US) (25.18 kg) |
|---------------------|-------------------------|

## Packing Units

|                              |                    |
|------------------------------|--------------------|
| Package 1 Height             | 8.98 in (22.8 cm)  |
| Package 1 width              | 15.47 in (39.3 cm) |
| Package 1 Length             | 29.96 in (76.1 cm) |
| Number of Units in Package 3 | 12                 |

## Offer Sustainability

|                           |                                                                                                                                                                                                                                                                                             |
|---------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation          | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                                                           |
| EU RoHS Directive         | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>                                                                                                                                                                                              |
| Take-back                 | Take-back program available                                                                                                                                                                                                                                                                 |

## Contractual warranty

|          |                          |
|----------|--------------------------|
| Warranty | 1 year repair or replace |
|----------|--------------------------|