



## Overview

Lead time	Usually in Stock
-----------	------------------

## Physical

Cable length	2 ft (0.61 m)
Color	Black
Depth	2.56 in (6.5 cm)
Height	11.81 in (30 cm)
Product Weight	3.00 lb(US) (1.36 kg)
Width	2.36 in (6 cm)

## Input

Plug standard	IEC 60320 C20
Number of cables	6
Max line current	16 A
Input current limits	16 A

## Output

Max current draw	16 A
Number of power socket outlets	1 IEC 60320 C19
Cord Length	2 ft (0.61 m)

## Conformance

Product Certifications	CCC CSA PSE UL Listed VDE
------------------------	---------------------------------------

## Environmental

Ambient Air Temperature for Operation	32...167 °F (0...75 °C)
Relative Humidity	20...80 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...167 °F (-25...75 °C)
Storage Relative Humidity	20...80 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

## Ordering and shipping details

GTIN	00731304324683
Package weight(Lbs)	3.00 lb(US) (1.36 kg)

## Packing Units

Package 1 Height	11.81 in (30 cm)
Package 1 width	2.36 in (6 cm)
Package 1 Length	2.56 in (6.5 cm)
Number of Units in Package 3	390

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Lead free	Yes
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------