



Overview

Presentation	Kit includes parts and fasteners to achieve Seismic level 2 certification
Lead time	Usually in Stock

Physical

Height	4.17 in (10.6 cm)
Width	27.56 in (70 cm)
Depth	32.17 in (81.7 cm)
Net Weight	55.12 lb(US) (25 kg)
Mounting Mode	Not rack-mountable

Conformance

Product Certifications	C-tick RCM
Standards	EN/IEC 62040-1 EN/IEC 62040-2 EN/IEC 62040-3 UL 1778

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Operating altitude	0...3333 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	-4...149 °F (-20...65 °C)
Storage altitude	0...49212 ft (0.00...14999.82 m)
Storage Relative Humidity	0...95 %

Ordering and shipping details

GTIN	731304320784
Package weight(Lbs)	59.52 lb(US) (27 kg)

Packing Units

Package 1 Height	5.98 in (15.2 cm)
Package 1 width	30.00 in (76.2 cm)
Package 1 Length	34.02 in (86.4 cm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	1 year (parts only)
----------	---------------------