



Main

Range	Square D X Series
Product or Component Type	Dimmer
Device Application	Control
Device presentation	Mechanism with fixing frame
Aesthetic name	X Series
Actuator	Slide
Colour tint	white

Complementary

Number of gangs	1 gang
Number of poles	1
Number of way	3
[Ie] rated operational current AC	15 A
[Ue] rated operational voltage	120 V
Network type	AC
Network Frequency	60 Hz
Load type	Halogen 5...500 W Incandescent 5...500 W Dimmable LED 0...150 W
Mounting Mode	By screws
Device mounting	Flush
Material	Plastic strap Metal fixing frame
Surface Finish	Matte
Connections - terminals	Phase and neutral 4 screw terminal copper Earth 1 screw terminal copper
Width	1.77 in (45 mm)
Height	4.06 in (103 mm)
Depth	1.97 in (50 mm)
Quantity per Set	1 piece

Environment

Product Certifications	cULus
Standards	UL 1472 NEMA SSL 7A

Ordering and shipping details

Category	09931-WD ADVANCED DEVICES
Discount Schedule	DE9
GTIN	785901534990
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.17 in (10.6 cm)
Package 1 Width	2.44 in (6.2 cm)
Package 1 Length	2.56 in (6.5 cm)
Package 1 Weight	6.28 oz (178.0 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	4.45 in (11.3 cm)
Package 2 Width	5.39 in (13.7 cm)
Package 2 Length	12.60 in (32.0 cm)
Package 2 Weight	4.23 lb(US) (1.919 kg)
Unit Type of Package 3	PAL
Number of Units in Package 3	1920
Package 3 Height	47.24 in (120.0 cm)
Package 3 Width	39.37 in (100.0 cm)
Package 3 Length	47.24 in (120.0 cm)
Package 3 Weight	908.68 lb(US) (412.171 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: carbon black, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	2 years
----------	---------