



### Overview

Lead time	Usually in Stock
-----------	------------------



### General

Provided equipment	Cat 5 ethernet cable User Manual
--------------------	-------------------------------------

### Physical

Cable length	4 ft (1.22 m)
Color	Beige
Depth	1.50 in (3.8 cm)
Height	12.99 in (33 cm)
Product Weight	0.79 lb(US) (0.36 kg)
Width	2.01 in (5.1 cm)

### Input

Input power	1200 W
Maximum Line Current per phase	15 A
Input Frequency	50/60 Hz +/- 5 Hz auto-sensing
Plug standard	NEMA 5-15P
Maximum Input Current per Phase	15 A
Switching current capacity	15 A
Nominal Input Voltage	120 V

### Output

Number of power socket outlets	6
Outlet standard	NEMA 5-15R

### Conformance

UL 1449 TVSS Rating	400
Product Certifications	ETL
Equipment protection policy	Lifetime : \$50000

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

## Surge Protection and Filtering

NM Surge Response Time (ns)	1 ns common mode
Common mode rejection	40 dB
Peak current	72 KA common mode 60 kA per phase normal mode
Surge energy rating	1080 J
Data line protection	RJ45 Modem/Fax/DSL/10-100 Base-T protection

## Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
GTIN	00731304282723
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No

## Packing Units

Package 1 Height	14.02 in (35.6 cm)
Package 1 width	4.80 in (12.2 cm)
Package 1 Length	1.81 in (4.6 cm)
SCC14	10731304282720
Number of Units in Package 2	6
Package 2 Weight	7.35 lb(US) (3.33 kg)
Package 2 Height	4.9 in (124.46 mm)
Package 2 width	11.5 in (292.10 mm)
Package 2 Length	14.9 in (378.46 mm)
Number of Units in Package 3	810

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: 1,3-Butadiene, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>

## Contractual warranty

Warranty	Limited Lifetime
----------	------------------