



Main

Range	TeSys
Product or Component Type	Undervoltage trip
Device short name	GV7AS
Device application	Control
Range compatibility	TeSys GV5 TeSys GV6 TeSys GV7

Complementary

[Uc] control circuit voltage	200...240 V AC 50/60 Hz
Control circuit voltage limits	0.85...1.1 Un
[Ui] rated insulation voltage	690 V AC IEC 60947-1 600 V AC UL 508 600 V AC CSA C22.2 No 14
Threshold tripping voltage	0.35...0.7 Ue
Inrush power in VA	10 VA AC
Hold-in Power Consumption in VA	5 VA AC
Operating time	< 50 ms IEC 60947-1
On-load factor	100 %
Connections - terminals	Screw clamp terminals 1 0.00 in ² (1 mm ²)flexible with cable end Screw clamp terminals 1 0.00 in ² (1.5 mm ²)flexible without cable end Screw clamp terminals 1 0.00 in ² (1.5 mm ²)solid
Tightening torque	1.2 N.m screw clamp terminals
Net Weight	0.23 lb(US) (0.105 kg)
Quantity per Set	Set of 10

Ordering and shipping details

Category	22366-MAN STR PROTECTORS-GV1/GV3
Discount Schedule	I11
GTIN	3389110566932
Nbr. of units in pkg.	1
Package weight(Lbs)	4.06 oz (115.0 g)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.57 in (4 cm)
Package 1 width	3.27 in (8.3 cm)
Package 1 Length	2.48 in (6.3 cm)
Unit Type of Package 2	CAR
Number of Units in Package 2	30
Package 2 Weight	8.19 lb(US) (3.715 kg)

Package 2 Height	17.13 in (43.5 cm)
Package 2 width	5.59 in (14.2 cm)
Package 2 Length	11.81 in (30 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------