

Product data sheet

Characteristics

8910DPA33V06

Contacteur, Definite Purpose, 30A, 3 pole, 20 HP at 575 VAC, 3 phase, 440/480 VAC 50/60 Hz coil, open



Main

Product or Component Type	Definite Purpose Contactor
Line Rated Current	30 A
Number of Poles	3P
Pole contact composition	3 NO
Range of Product	DPA

Complementary

Maximum Horse Power Rating	2 Hp 115 V AC, 1 phase 5 Hp 230 V AC, 1 phase 10 Hp 230 V AC, 3 phase 15 Hp 460 V AC, 3 phase 20 hp 575 V AC, 3 phase
Locked rotor rated current	150 A 460 V AC 120 A 575 V AC 180 A 277 V AC
[Ue] rated operational voltage	600 V AC
[Uc] control circuit voltage	440 V AC 50 Hz 480 V AC 60 Hz
Phase	3 phase
Electrical Connection	Binder head Quick connect terminals

Environment

Product Certifications	UL Recognized CSA
------------------------	----------------------

Ordering and shipping details

Category	21343-8910 DPA 3_(30 AMP)
Discount Schedule	CP1B
GTIN	785901849841
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.50 in (6.35 cm)
Package 1 Width	3.20 in (8.128 cm)
Package 1 Length	4.20 in (10.668 cm)
Package 1 Weight	17.44 oz (494.416 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	8

Package 2 Height	7.00 in (17.78 cm)
Package 2 Width	5.80 in (14.732 cm)
Package 2 Length	8.70 in (22.098 cm)
Package 2 Weight	8.89 lb(US) (4.032 kg)

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------