

RACSC101

InRow SC System 1 InRow SC, 1 NetShelter
SX Rack 600mm, and Rear Containment



Overview

Lead time	Special Order - Call for Quoted Lead Times
-----------	--

Main

Main Input Voltage	208 V 220 V 230 V 240 V
Plug standard	NEMA L6-20P
Number of rack unit	42U
Number of cables	1
Provided Equipment	Installation guide

General

Compressor Type	Rotary
Air Discharge Patterns	Horizontal
Intake Air	Rear Return
Refrigerant Charge	3 lb(US) (1.36 kg)
Air flow	1200 ft ³ /min (566.34 l/s)
Inrush current	56 A
Condensate Pump Capacity	1.3 Gal/hr(US) (0.00 m3/h)

Physical

Color	Black
Height	78.39 in (199.1 cm)
Width	35.43 in (90 cm)
Depth	50.12 in (127.3 cm)
Net Weight	731.23 lb(US) (331.68 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Input power	2940 W
Input Frequency	60 Hz

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environmental

Ambient Air Temperature for Storage	32...104 °F (0...40 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...15000 ft (0.00...4572.00 m)
Acoustic level	80 dBA

Communications & Management

Control panel	Multi-function LCD status and control console
---------------	---

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Lead free	Yes

Contractual warranty

Warranty	1 year (parts only)
----------	---------------------