



## Main

Range	TeSys
Product or component type	Undervoltage trip
Device short name	GV7AS
Device application	Control
Range compatibility	TeSys GV5 TeSys GV6 TeSys GV7

## Complementary

[Uc] control circuit voltage	110...130 V AC 50/60 Hz
Control circuit voltage limits	0.85...1.1 Un
[Ui] rated insulation voltage	690 V AC IEC 60947-1 600 V AC UL 508 600 V AC CSA C22.2 No 14
Threshold tripping voltage	0.35...0.7 Ue
Inrush power in VA	10 VA AC
Hold-in power consumption in VA	5 VA AC
Operating time	< 50 ms IEC 60947-1
On-load factor	100 %
Connections - terminals	Screw clamp terminals 1 0.00 in <sup>2</sup> (1 mm <sup>2</sup> )flexible with cable end Screw clamp terminals 1 0.00 in <sup>2</sup> (1.5 mm <sup>2</sup> )flexible without cable end Screw clamp terminals 1 0.00 in <sup>2</sup> (1.5 mm <sup>2</sup> )solid
Tightening torque	1.2 N.m screw clamp terminals
Net Weight	0.23 lb(US) (0.105 kg)
Quantity per set	Set of 10

## Ordering and shipping details

Category	22366 - MAN STR PROTECTORS-GV1/GV3
Discount Schedule	I11
GTIN	00785901375272
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	FR

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.57 in (4 cm)
Package 1 width	2.48 in (6.3 cm)
Package 1 Length	3.27 in (8.3 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

## Contractual warranty

Warranty	18 months
----------	-----------