

Main

Product Range	Harmony Electromechanical Relays
Product Type	Protection module
Product Compatibility	Socket 70-781 plug-in Socket 70-782 plug-in
Device Application	Protection

Complementary

[Ue] rated operational voltage	120 V
Protection Technology	MOV
Width	0.49 in (12.45 mm)
Depth	0.34 in (8.64 mm)


Ordering and shipping details

GTIN	3606480278334
------	---------------

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Wiring Diagram



- (1) : MOV Suppressor
(2) : Protection Diode
(3) : LED Indicator
(4) : RC Suppressor