

# Product data sheet

Specifications



license, Ecostruxure Machine Expert, professional, floating, site, 100 users

ESECAPCZZEPBZZ

## Main

|                              |                                                                                                               |
|------------------------------|---------------------------------------------------------------------------------------------------------------|
| Range of product             | EcoStruxure Machine Expert                                                                                    |
| Product or component type    | License                                                                                                       |
| Format                       | Digital                                                                                                       |
| Software type                | Professional                                                                                                  |
| Type of license              | Floating license                                                                                              |
| Software version             | V2.2                                                                                                          |
| Operating system requirement | Windows 10 64 bit<br>Windows 11 64 bit                                                                        |
| User language                | English<br>Spanish<br>Chinese<br>French<br>German<br>Italian<br>Portuguese (Brazilian)<br>Turkish<br>Japanese |

## Complementary

|                   |                                |
|-------------------|--------------------------------|
| License category  | Permanent                      |
| Software function | Engineering<br>Programming PLC |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
|-----------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Range compatibility         | Modicon M241<br>Modicon M251<br>Modicon M262<br>Modicon TM3<br>Modicon TM5<br>Modicon TM7<br>PacDrive LMC Eco<br>PacDrive LMC Pro<br>PacDrive LMC Pro2<br>Preventa XPSMC<br>Preventa XPSMCM<br>Lexium 32<br>Lexium 32i<br>Lexium 32M<br>Lexium 52<br>Lexium 62<br>Lexium ILA<br>Lexium ILE<br>Lexium ILS<br>Lexium SD3<br>Altivar 320<br>Altivar 340<br>Altivar Process ATV600<br>Altivar Easy 610<br>Altivar 660 Drive System<br>Altivar Process ATV900<br>Altivar Process 980 Regenerative Drive System<br>Harmony XB5R<br>Harmony XB4R<br>OsiSense XG<br>OsiSense XUW<br>TeSys U<br>TeSys T<br>TeSys island<br>Magelis XBT GH<br>Magelis GTO<br>Magelis GTU<br>Magelis GTUX<br>Magelis iPC<br>Magelis STO & STU<br>Magelis GK<br>Magelis SCU<br>EcoStruxure Machine Expert Twin |
| Communication port protocol | Modbus SL<br>Modbus TCP<br>EtherNet/IP<br>CANopen<br>Sercos III<br>CANmotion                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
| Hosting option              | On-premise                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
| License size                | Entity (100 users)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| System requirements         | 8 GB RAM<br>15 GB hard disk space                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| Processor requirement       | Intel Core 2 Duo                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |
| Display resolution          | 1280 x 1024 pixels                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |

## Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type of Package 1       | PCE      |
| Number of Units in Package 1 | 1        |
| Package 1 Height             | 0.1 cm   |
| Package 1 Width              | 0.1 cm   |
| Package 1 Length             | 0.1 cm   |
| Package 1 Weight             | 0.001 kg |