

Product data sheet

Characteristics

8910DP32V09

Contacteur, Definite Purpose, 30A, 2 pole, 208/240VAC coil at 60Hz, 220VAC coil at 50Hz, open



Main

| | |
|---------------------------|----------------------------|
| Product or Component Type | Definite Purpose Contactor |
| Line Rated Current | 30 A |
| Number of Poles | 2P |
| Pole contact composition | 2 NO |
| Range of Product | DP |

Complementary

| | |
|--------------------------------|--|
| Maximum Horse Power Rating | 2 Hp 115 V AC, 1 phase 5 hp 230 V AC, 1 phase |
| Locked rotor rated current | 125 A 460 V AC 100 A 575 V AC 150 A 277 V AC |
| [Ue] rated operational voltage | 600 V AC |
| [Uc] control circuit voltage | 208...240 V AC 60 Hz 220 V AC 50 Hz |
| Phase | 1 phase |
| Electrical Connection | Binder head Quick connect terminals |

Environment

| | |
|------------------------|----------------------|
| Product Certifications | UL Recognized CSA |
|------------------------|----------------------|

Ordering and shipping details

| | |
|-------------------|------------------|
| Category | 21356-8910 DP 32 |
| Discount Schedule | CP1B |
| GTIN | 785901073345 |
| Returnability | Yes |
| Country of origin | CN |

Packing Units

| | |
|------------------------------|---------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 2.60 in (6.604 cm) |
| Package 1 Width | 3.40 in (8.636 cm) |
| Package 1 Length | 2.30 in (5.842 cm) |
| Package 1 Weight | 8.16 oz (231.332 g) |

Offer Sustainability

| | |
|----------------------------|---|
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|