

## Product data sheet

### Characteristics

## 8911DP53V09

Starter, Definite Purpose, nonreversing, 50A,  
3 pole, 3 phase, 208 to 240 VAC coil, melting  
alloy overload, NEMA 1



### Main

|                         |                                                                                                                                    |
|-------------------------|------------------------------------------------------------------------------------------------------------------------------------|
| Product                 | Definite Purpose Starter                                                                                                           |
| Ampere Rating           | 50 A                                                                                                                               |
| Horsepower Rating       | 3 Hp 115 V AC, 1 phase<br>10 Hp 230 V AC, 1 phase<br>15 Hp 230 V AC, 3 phase<br>30 Hp 460 V AC, 3 phase<br>30 hp 575 V AC, 3 phase |
| Maximum Voltage Rating  | 600 V AC                                                                                                                           |
| Control Circuit Voltage | 220 V AC 50 Hz<br>208...240 V AC 60 Hz                                                                                             |
| Phase                   | 3 phase                                                                                                                            |

### Complementary

|                         |                                                    |
|-------------------------|----------------------------------------------------|
| Enclosure Material      | Painted sheet steel                                |
| Enclosure Rating        | NEMA 1                                             |
| Locked Rotor Amperes    | 300 A 230 V AC<br>250 A 460 V AC<br>200 A 575 V AC |
| Number of Poles         | 3P                                                 |
| Range                   | DPS                                                |
| Overload Type           | Melting alloy                                      |
| Number of Thermal Units | 3                                                  |

### Ordering and shipping details

|                   |               |
|-------------------|---------------|
| Category          | 21381-8911 DP |
| Discount Schedule | CP1           |
| GTIN              | 785901025108  |
| Returnability     | Yes           |
| Country of origin | CN            |

### Packing Units

|                              |                        |
|------------------------------|------------------------|
| Unit Type of Package 1       | PCE                    |
| Number of Units in Package 1 | 1                      |
| Package 1 Height             | 7.20 in (18.288 cm)    |
| Package 1 Width              | 7.50 in (19.05 cm)     |
| Package 1 Length             | 20.50 in (52.07 cm)    |
| Package 1 Weight             | 9.50 lb(US) (4.309 kg) |

### Offer Sustainability

|                            |                                               |
|----------------------------|-----------------------------------------------|
| REACH Regulation           | <a href="#">REACH Declaration</a>             |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a> |
| Mercury free               | Yes                                           |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>        |
| RoHS exemption information | Yes                                           |

Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|