



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	120 V
Plug standard	NEMA 5-15P
Cable length	6 ft (1.83 m)
Number of cables	1
Provided equipment	2 x 1.8 Meter Tel cable User Manual

Physical

Color	Beige
Height	2.01 in (5.1 cm)
Width	4.25 in (10.8 cm)
Depth	10.51 in (26.7 cm)
Net Weight	1.81 lb(US) (0.82 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Maximum Line Current per phase	15 A
Input Frequency	50/60 Hz +/- 5 Hz auto-sensing

Output

Number of power socket outlets	7
Outlet standard	NEMA 5-15R

Conformance

UL 1449 TVSS Rating	330
Product Certifications	CSA
Standards	UL 497A UL 1283 UL 1363 UL 1449
Equipment protection policy	Lifetime : \$50000

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Surge Protection and Filtering

EP Joule Rating	1060 J
Data Lines Protected (multi-line only)	1
NM Surge Response Time (ns)	0 ns common mode
Common mode rejection	60 dB
Peak current	13 KA common mode 6.5 kA normal mode
Surge energy rating	840 J
Data line protection	RJ11 Modem/Fax/DSL protection (two wire single line)

Ordering and shipping details

GTIN	731304000129
Package weight(Lbs)	2.31 lb(US) (1.05 kg)

Packing Units

Package 1 Height	2.09 in (5.3 cm)
Package 1 width	7.24 in (18.4 cm)
Package 1 Length	12.76 in (32.4 cm)
SCC14	10731304000126
Number of Units in Package 2	12
Package 2 Weight	27.8 lb(US) (12.61 kg)
Number of Units in Package 3	384

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: 1,3-Butadiene, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	Limited Lifetime
----------	------------------