

Product data sheet

Specifications



Safety switch, VisiPacT, heavy duty, unfused, viewing window, NEMA 1, 600V, 30A, 3 pole, ground lugs

VHU361GL

Product availability: Stock - Normally stocked in distribution facility

Main

Product	Single Throw Safety Switch
Duty Rating	Heavy duty
Device Application	Heavy application
Disconnect Type	Non-fusible disconnect
Factory Installed Neutral	Field installed kit available
Number of Poles	3
Current Rating	30 A
Voltage Rating	600 V AC/DC
Enclosure Rating	NEMA 1 steel
Standard Motor Power Rating	5 hp at 240 V AC 50/60 Hz for 1 phase motors 10 hp at 240 V AC 50/60 Hz for 3 phase motors 7.5 hp at 480 V AC 50/60 Hz for 1 phase motors 20 hp at 480 V AC 50/60 Hz for 3 phase motors 10 hp at 600 V AC 50/60 Hz for 1 phase motors 30 hp at 600 V AC 50/60 Hz for 3 phase motors 5 hp at 250 V DC 15 hp at 600 V DC

Complementary

Wiring configuration	3-wire
Wire Size	AWG 12...AWG 6 aluminium AWG 14...AWG 6 copper
Tightening torque	45 lbf.in (5.08 N.m) 0.02 in² (13.3 mm²) (AWG 6) 40 lbf.in (4.5 N.m) 0.013 in² (8.367 mm²) (AWG 8) 35 lbf.in (4.0 N.m) 0.003...0.008 in² (2.06...5.261 mm²) (AWG 14...AWG 10)
Depth	5.11 in (129.79 mm)
Width	6.36 in (161.54 mm)
Height	14.57 in (370.08 mm)
Net Weight	8.8 lb(US) (4 kg)
Grounding Kit	Factory installation
Service Entrance	Suitable service entrance for USA Suitable service entrance for Mexico

Environment

Certifications	UL listed file E2875
----------------	----------------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	UL98 CSA C22.2 No 4 NOM-003-SCFI-2000
-----------	---

Ordering and shipping details

Category	US10DE100008
Discount Schedule	0DE1
GTIN	3606485895048
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	5.00 in (12.7 cm)
Package 1 Width	7.50 in (19.05 cm)
Package 1 Length	15.62 in (39.687 cm)
Package weight(Lbs)	8.8 lb(US) (4 kg)

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	37
Environmental Disclosure	Product Environmental Profile

Use Better


Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant
REACH Regulation	REACH Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

Technical Illustration


Dimensions



ALL DIMENSIONS ARE APPROXIMATE.
REFER TO TECHNICAL DRAWINGS AND DOCUMENTATION FOR KNOCKOUTS AND ADDITIONAL INFORMATION.

Technical Illustration

Wiring diagram



CATALOG NO. VHU361GL
REFER TO TECHNICAL DRAWINGS AND DOCUMENTATION FOR COMPLETE INFORMATION.