

Product data sheet

Characteristics

8501RS41P14V14

Plug in relay, Type R, miniature, 1 HP at 277 VAC, 15A resistive at 120 VAC, 5 blade, SPDT, 1 NO, 1 NC, 24 VAC coil



Main

Product range	8501R
Product type	Miniature Relay
Relay Type	Standard

Complementary

Mounting type	Socket
Contact composition	SPDT
[Uc] control circuit voltage	24 V AC
Pilot light	Green indicator relay energised LED
Manual operator	Without test button
Horsepower rating	0.5 120 V AC 1 277 V AC
Breaking capacity	3 A 120 V AC inductive control circuit UL 508 1.5 A 240 V AC inductive control circuit UL 508 15 A 120 V AC resistive control circuit UL 508 10 A 277 V AC resistive control circuit UL 508 15 A 28 V DC resistive control circuit UL 508
Maximum switching voltage	300 V AC 30 V DC
Contact material	Silver alloy, gold flashed
Operating time	20 ms - pick-up 20 ms - drop-out
Shape of pins	Spade
For use with	8501NR41
Height	1.07 in (27.3 mm)
Width	0.55 in (14 mm)
Depth	1.65 in (41.8 mm)

Environment

Ambient temperature range - operational	-40...131 °F (-40...55 °C)
Product certifications	UL Listed UL Recognized CSA CE

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	21143-8501 R
Discount Schedule	CP2
GTIN	785901218470
Returnability	No
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.00 in (2.54 cm)
Package 1 Width	1.00 in (2.54 cm)
Package 1 Length	2.00 in (5.08 cm)
Package 1 Weight	0.80 oz (22.68 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------