

Product data sheet

Characteristics

8910DP31V02

Contactor, Definite Purpose, 30A, 1 pole,
110/120 VAC 50/60 Hz coil, open



Main

Product or Component Type	Definite Purpose Contactor
Line Rated Current	30 A
Number of Poles	1P
Pole contact composition	1 NO
Range of Product	DP

Complementary

Maximum Horse Power Rating	2 Hp 115 V AC, 1 phase 3 hp 230 V AC, 1 phase
Locked rotor rated current	125 A 460 V AC 100 A 575 V AC 150 A 277 V AC
[Ue] rated operational voltage	600 V AC
[Uc] control circuit voltage	120 V AC 60 Hz 110 V AC 50 Hz
Phase	1 phase
Electrical Connection	Quick connect terminals Binder head

Environment

Product Certifications	UL Recognized CSA
------------------------	----------------------

Ordering and shipping details

Category	21355-8910 DP 31
Discount Schedule	CP1B
GTIN	785901909378
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.50 in (6.35 cm)
Package 1 Width	2.30 in (5.842 cm)
Package 1 Length	3.50 in (8.89 cm)
Package 1 Weight	8.16 oz (231.332 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	12
Package 2 Height	5.80 in (14.732 cm)
Package 2 Width	7.00 in (17.78 cm)
Package 2 Length	7.10 in (18.034 cm)
Package 2 Weight	6.37 lb(US) (2.889 kg)

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------