

Product data sheet

Characteristics

8911DP SG42V09

Starter, Definite Purpose, nonreversing, 40A,
2 pole, 1 phase, 208 to 240VAC coil, melting
alloy overload, NEMA 1



Main

Product	Definite Purpose Starter
Ampere Rating	40 A
Horsepower Rating	3 Hp 115 V AC, 1 phase 7.5 hp 230 V AC, 1 phase
Maximum Voltage Rating	600 V AC
Control Circuit Voltage	220 V AC 50 Hz 208...240 V AC 60 Hz
Phase	1 phase

Complementary

Enclosure Material	Painted sheet steel
Enclosure Rating	NEMA 1
Locked Rotor Amperes	240 A 230 V AC 200 A 460 V AC 160 A 575 V AC
Number of Poles	2P
Range	DPS
Overload Type	Melting alloy
Number of Thermal Units	1

Ordering and shipping details

Category	21381-8911 DP
Discount Schedule	CP1
GTIN	785901724766
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.50 in (16.51 cm)
Package 1 Width	7.00 in (17.78 cm)
Package 1 Length	11.30 in (28.702 cm)
Package 1 Weight	5.83 lb(US) (2.644 kg)

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------