



Overview

Lead time	Special Order - Call for Quoted Lead Times
-----------	--

Physical

Cable length	4 ft (1.22 m)
Color	Black
Depth	1.77 in (4.5 cm)
Height	9.45 in (24 cm)
Product Weight	2.23 lb(US) (1.01 kg)
Width	2.76 in (7 cm)

Input

Plug standard	IEC 60320 C14
Number of cables	6
Max line current	10 A
Input current limits	10 A

Output

Max current draw	10 A
Number of power socket outlets	1 IEC 60320 C13
Cord Length	4 ft (1.22 m)

Conformance

Product Certifications	CSA UL Listed
------------------------	------------------

Environmental

Ambient Air Temperature for Operation	32...221 °F (0...105 °C)
Relative Humidity	20...80 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...221 °F (-25...105 °C)
Storage Relative Humidity	20...80 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	00731304335542
Package weight(Lbs)	2.23 lb(US) (1.01 kg)

Packing Units

Package 1 Height	9.45 in (24 cm)
Package 1 width	2.76 in (7 cm)
Package 1 Length	1.77 in (4.5 cm)
Number of Units in Package 3	390

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------